

KLIMAS Sp. z o.o. ul. W. Witosa 135/137 Kuźnica Kiedrzyńska 42-233 Mykanów tel. +48 34 377 71 00, fax. +48 34 328 01 73 Infolinia: 801 477 477, www.wkret-met.com.pl



PRODUCT DATA SHEET – WHO/WHOW

Section 1. PRODUCT DESCRIPTION



- 1. Original screws delivered by the manufacturer can be used only
- 2. Before installation identify a substrate in which the screw will be installed and compare loads which the screw will carry to resistance values given in Product Data Sheet or National Technical Assessment
- 3. Select adequate screw length, depending on thickness of members being fixed
- 4. Use proper method of drilling according to a substrate type (holes in masonry substrate made of autoclaved aerated concrete blocks should be drilled using a drill without impact)
- 5. Diameter of drilled holes should match diameter of hole recommended by the manufacturer
- 6. Drilled holes in substrates of solid materials should be deeper by min. 10mm compared to the screw anchorage depth
- 7. Clean the holes in solid materials of drillings with a back and forth motion of the drill at a reduced speed
- 8. Fixing is executed by driving the screw using screw gun with adequate bit (TORX-30)



Section 3. TECHNICAL DATA

TECHNICAL PARAMETERS			
Parameter	Unit	Value	
		WHO	WHOW
Screw diameter	d _k [mm]	7,5	
Hole/drill diameter	d₀ [mm]	6	
Effective anchorage depth	h _{eff} [mm]	30/40/60*	
Drilled hole depth	h₀ [mm]	40/50/70*	
Drive type	[-]	TORX-30	
Screw material	[-]	Zinc-plated steel	
National Technical Assessment	[-]	ITB-KOT-2017/0308	

*for concrete / solid brick / autoclaved aerated concrete

RESISTANCE				
Culturbrates to us a	Design resistance – WHO/WHOW			
Substrate type	Pull-out [kN]	Shear [kN]		
Concrete C20/25 – C50/60	1,19	2,40		
Solid clay brick	0,80	1,60		
Autoclaved aerated concrete	0,20	0,40		

INSTALLATION PARAMETERS				
Substrate type	Min. substrate thickness	Min. distance from edge	Min. axial distance	
	h _{min} [mm]	c _{min} [mm]	L _{os} [mm]	
Concrete C20/25 – C50/60	80	45	250	
Solid clay brick	80	60	250	
Autoclaved aerated concrete	90	90	250	

1

All rights reserved The sheet may be disclosed only in the form as delivered. No part (contents such as text, graphics, logos, figures, pictures, and any other data) given in this document may be modified or published whatsoever in part, without prior authorisation. Any trademarks, graphic symbols, trade names, logos and other data are protected by copyright and are property of their owner. Created: 2013-10-16 Updated: 2023-04-28





Wkręt-met KLIMAS

PRODUCT DATA SHEET – WHO/WHOW





SELECTION TABLE – WHO				
Product code	Screw diameter and length	Head diameter	Drive type	Number of pieces in a box
	d _{wx} L _w [mm]	D _w [mm]	[-]	[pcs]
WHO-75042	7,5x42	11	TORX-30	200
WHO-75062	7,5x62	11	TORX-30	200
WHO-75082	7,5x82	11	TORX-30	100
WHO-75102	7,5x102	11	TORX-30	100
WHO-75112	7,5x112	11	TORX-30	100
WHO-75132	7,5x132	11	TORX-30	100
WHO-75152	7,5x152	11	TORX-30	100
WHO-75182	7,5x182	11	TORX-30	100
WHO-75212	7,5x212	11	TORX-30	100

SELECTION TABLE – WHOW				
Product code	Screw diameter and length	Head diameter	Drive type	Number of pieces in a box
	d _{w x} L _w [mm]	D _w [mm]	[-]	[pcs]
WHOW-75042	7,5x42	8,5	TORX-30	200
WHOW-75062	7,5x62	8,5	TORX-30	200
WHOW-75082	7,5x82	8,5	TORX-30	100
WHOW-75102	7,5x102	8,5	TORX-30	100
WHOW-75112	7,5x112	8,5	TORX-30	100
WHOW-75132	7,5x132	8,5	TORX-30	100
WHOW-75152	7,5x152	8,5	TORX-30	100
WHOW-75182	7,5x182	8,5	TORX-30	100
WHOW-75212	7,5x212	8,5	TORX-30	100

SECTION 4. REMARKS

- 1. All previous versions of this Product Data Sheet shall cease to be valid
- 2. Data given in this Product Data Sheet is in accordance with current knowledge and published in good faith. KLIMAS Sp. z o.o. is not responsible for correctness and quality of the fixing if recommendations regarding method of use and installation are not followed.